

Polyamide/PEEK

Polyamide/PEEK

Polyamide/PEEK

PA  
PEEK

Vorpolitur • pre-polishing • pré polissage



Glanzpolitur • shine polishing • poli brillant



Hochglanzpolitur • high shine polishing • lustrage



Info

4280	= Ø 80 mm	= 1.400 rpm
869 100/14	= Ø 100 mm	= 1.400 rpm
868 4'' x 50 H	= Ø 100 mm	= 1.400 rpm



ThermoPol Set

- Inhalt/contents/ contenu  
 1 x Polistar Lintygrau 90g  
 2 x 4280  
 1 x Polistar Creme 90g  
 1 x 869 100/14  
 1 x Polistar pro Rosa 150g  
 1 x 868 4''x 50 H  
 1 x PocketCard

Zirkoniumdioxid

Zirconium dioxide

Dioxyde de zirconium

ZrO<sub>2</sub>

Fein schleifen • Finest grinding • rectifiage fin












Hochglanzpolitur • high shine polishing • lustrage



Info

362 4 HP	= Ø 4 mm	= 10.000 rpm
TORO 5 100	= Ø 17,5 mm	= 10.000 rpm

PMMA/Komposite	PMMA/Composite	PMMA/Composite	
<b>PMMA COMPOSITE</b>	Vorpolitur • pre-polishing • pré polissage		
	905.1 14 PP 	→ 	→ 
	Glanzpolitur • shine polishing • poli brillant		
903.2 14 PP 	→ 	→ 	
Hochglanzpolitur • high shine polishing • lustrage			
904.3 14 PP 	→ 	→ 	

**Info**

905.1 14 PP = Ø 14 mm = 5.000 rpm  
 903.2 14 PP = Ø 14 mm = 5.000 rpm  
 904.3 14 PP = Ø 14 mm = 5.000 rpm



**HABRAS Disc Pro DCS Kit 14**  
 Inhalt/contents/contenu  
 1 x 905.1 14 PP  
 1 x 903.2 14 PP  
 1 x 904.3 14 PP

Lithiumdisilikat	Lithium disilicate	Silicate de lithium	
<b>LiSi<sub>2</sub></b>	Feinstschleifen • Finest grinding • rectifiage fin		
	367 4 HP 	→ 	→ 
Hochglanzpolitur • high shine polishing • lustrage			
TORO 5 102 	+ 	→ 	→ 

**Info**

367 4 HP = Ø 4 mm = 10.000 rpm  
 TORO 5 102 = Ø 17,5 mm = 10.000 rpm